





Timing Relay, Type JCK, plug In, on delay, fixed time, 3 seconds, 10A, 240 VAC, 120 VAC/110 VDC

9050JCK1F3V20

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 78.00 USD

Main

| Product Range | 9050JCK |
|----------------|----------------------|
| Product Type | Timer |
| Timing Mode | On-delay |
| Timing Range | 3 s |
| Supply Voltage | 120 V AC 110 V DC |

Complementary

| Power Consumption | 2 VA |
|---------------------------|----------------------|
| Current Rating | 10 A |
| Switch Function | DPDT |
| Contact Composition | 2 NO + 2 NC |
| Contact Material | Silver nickel |
| Maximum Switching Voltage | 240 V AC |
| Mounting Type | Socket |
| Number Of Pins | 8 |
| Shape Of Pins | Tubular |
| For Use With | 8501NR52 8501NR51 |

Environment

| Certifications | UL Recognized UL Listed CE |
|---|----------------------------------|
| Ambient Temperature Range - Operational | -18150 °F (-2866 °C) |
| Height | 2.40 in (61 mm) |
| Width | 1.69 in (43 mm) |
| Depth | 4.09 in (104 mm) |

Ordering and shipping details

| Category | US10CP221651 |
|-------------------|--------------|
| Discount Schedule | 0CP2 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Gtin | 785901056485 |
|-------------------|--------------|
| Returnability | Yes |
| Country Of Origin | US |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 4.50 in (11.43 cm) |
| Package 1 Width | 2.60 in (6.604 cm) |
| Package 1 Length | 2.00 in (5.08 cm) |
| Package 1 Weight | 5.28 oz (149.685 g) |

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| Ø | Reach Free Of Svhc | |
|----------|----------------------------|-----|
| ② | Toxic Heavy Metal Free | |
| 9 | Mercury Free | |
| ⊘ | Rohs Exemption Information | Yes |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|--------------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |