SQUARE 11





Plug In Timer, interval, 0.1 to 10 seconds, 12 VAC/DC

9050JCK31V36

! Discontinued on: Jan 29, 2021

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Range	9050JCK
Product Type	Timer
Timing Mode	Interval
Timing Range	0.110 s
Supply Voltage	12 V AC/DC

Complementary

Power Consumption	2 VA
Current Rating	10 A
Switch Function	DPDT
Contact Composition	2 NO + 2 NC
Contact Material	Silver nickel
Maximum Switching Voltage	240 V AC
Mounting Type	Socket
Number Of Pins	8
Shape Of Pins	Tubular
For Use With	8501NR51 8501NR52

Environment

Certifications	CE UL Recognized UL Listed
Ambient Temperature Range - Operational	-18150 °F (-2866 °C)
Height	2.40 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

Ordering and shipping details

Category	US10CP221651
Discount Schedule	0CP2
Gtin	00785901056652

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Returnability	No	
Country Of Origin	US	

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information