





Plug In Timer, interval, 300 seconds fixed, 120 VAC 110 VDC

9050JCK3F300V20

! Discontinued on: Jan 23, 2021

① Discontinued

Main

9050JCK	
Timer	
Interval	
300 s	
120 V AC	
_	Timer Interval 300 s

Complementary

Power Consumption	2 VA	
Current Rating	10 A	
Switch Function	DPDT	
Contact Composition	2 NO + 2 NC	
Contact Material	Silver nickel	
Maximum Switching Voltage	240 V AC	
Mounting Type	Socket	
Number Of Pins	8	
Shape Of Pins	Tubular	
For Use With	8501NR52 8501NR51	

Environment

Certifications	UL Recognized CE UL Listed
Ambient Temperature Range - Operational	-18150 °F (-2866 °C)
Height	2.40 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

Ordering and shipping details

Category	21651-9050 JCK(NOT JCK60, 70) G P TIMERS
Discount Schedule	CP2
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin

Contractual warranty

US

18 months

Warranty



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
9	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information