## **Product data sheet**

Specifications



## Timing Relay, Type JCK, plug In, one shot, adjustable time, 0.1 to 10 seconds, 10A, 240 VAC, 120 VAC/110 VDC

9050JCK41V20

() Discontinued on: Oct 9, 2023

# Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Range	9050JCK	
Product Type	Timer	
Timing Mode	One shot	
Timing Range	0.110 s	
Supply Voltage	120 V AC 110 V DC	

#### Complementary

• •		
Power Consumption	2 VA	
Current Rating	10 A	
Switch Function	DPDT	
Contact Composition	2 NO + 2 NC	
Contact Material	Silver nickel	
Maximum Switching Voltage	240 V AC	
Mounting Type	Socket	
Number Of Pins	11	
Shape Of Pins	Tubular	
For Use With	8501NR61 8501NR62	

#### Environment

Certifications	UL Recognized CE UL Listed
Ambient Temperature Range - Operational	-18150 °F (-2866 °C)
Height	2.40 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

#### Ordering and shipping details

Category

US10CP221651

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Discount Schedule	0CP2
Gtin	785901056799
Returnability	Yes
Country Of Origin	US

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.60 in (6.604 cm)
Package 1 Width	4.40 in (11.176 cm)
Package 1 Length	1.90 in (4.826 cm)
Package 1 Weight	4.16 oz (117.934 g)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information