





Timing Relay, Type JCK, plug In, one shot, adjustable time, 0.3 to 30 seconds, 10A, 240 VAC, 120 VAC/110 VDC

9050JCK42V20

Product availability: Stock - Normally stocked in distribution facility

Price*: 98.00 USD

Main

Product Range	9050JCK	
Product Type	Timer	
Timing Mode	One shot	
Timing Range	0.330 s	
Supply Voltage	120 V AC 110 V DC	

Complementary

Power Consumption	2 VA
Current Rating	10 A
Switch Function	DPDT
Contact Composition	2 NO + 2 NC
Contact Material	Silver nickel
Maximum Switching Voltage	240 V AC
Mounting Type	Socket
Number Of Pins	11
Shape Of Pins	Tubular
For Use With	8501NR62 8501NR61

Environment

Certifications	CE UL Recognized UL Listed
Ambient Temperature Range - Operational	-18150 °F (-2866 °C)
Height	2.40 in (61 mm)
Width	1.69 in (43 mm)
Depth	4.09 in (104 mm)

Ordering and shipping details

Category US10CP221651

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Discount Schedule	0CP2	
Gtin	785901032922	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.00 in (5.08 cm)
Package 1 Width	2.50 in (6.35 cm)
Package 1 Length	4.50 in (11.43 cm)
Package 1 Weight	5.28 oz (149.685 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	4.50 in (11.43 cm)
Package 2 Width	10.00 in (25.4 cm)
Package 2 Length	11.00 in (27.94 cm)
Package 2 Weight	5.50 lb(US) (2.495 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
⊘	Toxic Heavy Metal Free	
⊘	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information