

Product data sheet

Specifications

SQUARE D

Green Premium™



Motor Logic solid state overload relay, NEMA Size 00, 3 to 9 A, 600 VAC

9065SFC20

Product availability : Stock - Normally stocked in distribution facility

Price* : 221.00 USD

Main

Range of Product Motor Logic

Thermal overload type Solid state

Complementary

NEMA size 00

Phase 3 phase

Mounting Support Mounting plate

[Ue] rated operational voltage 600 V AC

Height 2.69 in (68.3 mm)

Width 3.26 in (82.8 mm)

Depth 3.90 in (99.1 mm)

Net Weight 1.21 lb(US) (0.55 kg)

Ordering and shipping details

Category 21662-9065 SOLID STATE OVERLOAD RELAYS

Discount Schedule CP1

GTIN 785901750031

Nbr. of units in pkg. 1

Package weight(Lbs) 15.52 oz (440.0 g)

Returnability Yes

Country of origin MX

Packing Units

Unit Type of Package 1 PCE

Package 1 Height 5.31 in (13.5 cm)

Package 1 width 5.39 in (13.7 cm)

Package 1 Length 6.10 in (15.5 cm)

* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
-----------------	-----------