

# Product data sheet

Specifications

**SQUARE** D

Green  
Premium™



## Overload Relay, Motor Logic, solid state overload relay, NEMA Size 3, 3 pole, 30A to 90A, 600VAC, replacement relay

9065ST320

**Product availability : Stock - Normally stocked in distribution facility**

**Price\* : 351.00 USD**

### Main

Range of Product	Motor Logic
Product destination	Starter
Thermal overload type	Solid state

### Complementary

NEMA size	3
Phase	3 phase
Mounting Support	Mounting plate
[Ue] rated operational voltage	600 V AC
Height	5.02 in (127.5 mm)
Width	5.33 in (135.4 mm)
Depth	4.45 in (113 mm)

### Ordering and shipping details

Category	21662-9065 SOLID STATE OVERLOAD RELAYS
Discount Schedule	CP1
GTIN	785901751946
Returnability	Yes
Country of origin	MX

### Packing Units

Unit Type of Package 1	Db
Number of Units in Package 1	1
Package 1 Height	5.90 in (14.986 cm)
Package 1 Width	7.20 in (18.288 cm)
Package 1 Length	7.30 in (18.542 cm)
Package 1 Weight	2.87 lb(US) (1.302 kg)

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Offer Sustainability

<b>Sustainable offer status</b>	Green Premium product
<b>California proposition 65</b>	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>Mercury free</b>	Yes
<b>China RoHS Regulation</b>	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>Environmental Disclosure</b>	<a href="#">Product Environmental Profile</a>
<b>Circularity Profile</b>	<a href="#">End of Life Information</a>
<b>PVC free</b>	Yes

## Contractual warranty

<b>Warranty</b>	18 months
-----------------	-----------

## Recommended replacement(s)