

Product data sheet

Specifications



Terminal block, Linergy, fuse holder, Class J, 60A, 600V, 3 pole

9080FB3621J

Product availability: Stock - Normally stocked in distribution facility

Price*: 75.00 USD

Main

Range	9080FB
Product	Fuse holder

Complementary

Current Rating	60 A
[Ue] Rated Operational Voltage	<= 600 V AC/DC
Fuse Type	J
Fuse Size	1.0625 x 2.375 in
Number Of Poles	3
Electrical Connection	Box lugs
Wire Gauge	AWG 14...AWG 2 copper or aluminium
Sccr	200 kA UL 512
Product Certifications	CSA file 70360 class 6225 01 UL listed file E40747 CCN IZLT CE
Operating Temperature	-40...257 °F (-40...125 °C)
Mounting Type	Surface mount
Block Material	Thermoplastic: block
Wire Stripping Length	0.5625 in (14.29 mm)
Terminal Tightening Torque	lugs 50 lbf.in (5.65 N.m) AWG 3...AWG 2 copper or aluminium lugs 45 lbf.in (5.08 N.m) AWG 6...AWG 4 copper or aluminium lugs 40 lbf.in (4.52 N.m) AWG 8 copper or aluminium lugs 35 lbf.in (3.95 N.m) AWG 12...AWG10 copper or aluminium lugs 35 lbf.in (3.95 N.m) AWG 14 copper
Height	4.07 in (103.38 mm)
Width	4.72 in (119.89 mm)
Depth	2.09 in (53.09 mm)

Ordering and shipping details

Category	US10CP121701
Discount Schedule	0CP1
Gtin	785901139669
Returnability	Yes
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.20 in (5.588 cm)
Package 1 Width	4.10 in (10.414 cm)
Package 1 Length	4.80 in (12.192 cm)
Package 1 Weight	12.48 oz (353.802 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	20
Package 2 Height	5.00 in (12.7 cm)
Package 2 Width	12.00 in (30.48 cm)
Package 2 Length	19.70 in (50.038 cm)
Package 2 Weight	15.87 lb(US) (7.199 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	