

Product data sheet

Specifications



Power distribution block, Linergy, 3 pole, 1 line, 6 load, 335A Cu, 270A Al, 600V

9080LBA363106

Product availability: Stock - Normally stocked in distribution facility

Price*: 122.00 USD

Main

Range	9080LB
Product	Power Distribution Block
Current Rating	335 A copper 270 A aluminium
Short Circuit Current Rating	65 kA

Complementary

Voltage Rating	600 V AC/DC
Mounting Type	Surface mount
Number Of Poles	3
Terminals Per Pole	1 line 6 load
Wire Size	Line 1, AWG 6...400 kcmil, copper or aluminium Load 6, AWG 14...AWG 2, copper or aluminium
Electrical Connection	Tin plated aluminium lugs
Sccr	65 kA UL 508 A
Ambient Air Temperature For Operation	-40...302 °F (-40...150 °C)
Block Material	Phenolic: block
Terminal Tightening Torque	Load lug 45 lbf.in (5.08 N.m) AWG 6...AWG 4 copper or aluminium Load lug 40 lbf.in (4.52 N.m) AWG 8 copper or aluminium Load lug 35 lbf.in (3.95 N.m) AWG 14 copper Load lug 50 lbf.in (5.65 N.m) AWG 2 copper or aluminium Load lug 35 lbf.in (3.95 N.m) AWG 12...AWG10 copper or aluminium Line lug 375 lbf.in (42.37 N.m) AWG 6...400 kcmil copper or aluminium
Wire Stripping Length	Line: 1.06 in (26.92 mm) Load: 0.56 in (14.22 mm) for top connection Load: 1 in (25.40 mm) for bottom connection
Height	4.75 in (120.65 mm)
Width	6.03 in (153.16 mm)
Depth	2.91 in (73.91 mm)
End Barrier	9080LB33
Net Weight	1.57 lb(US) (0.71 kg)

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Certifications	CSA file 70361 class 6228 01 CE UL recognized E60616 CCN XCFR2
----------------	--

Ordering and shipping details

Category	US10CP121711
Discount Schedule	0CP1
Gtin	785901097471
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.00 in (7.62 cm)
Package 1 Width	4.40 in (11.176 cm)
Package 1 Length	5.30 in (13.462 cm)
Package 1 Weight	25.12 oz (712.14 g)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	16
Package 2 Height	10.90 in (27.686 cm)
Package 2 Width	9.50 in (24.13 cm)
Package 2 Length	13.30 in (33.782 cm)
Package 2 Weight	26.34 lb(US) (11.948 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration	
Eu Rohs Directive	Compliant EU RoHS Declaration	
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	