# **Product data sheet**

Specification



Acti9 - comb busbar - 3L balanced wtih Aux - 18 mm pitch - 57 modules

A9XAH657

#### Main

Range	Acti9	
Product Or Component Type	Comb busbar	
Mounting Mode	Horizontal	
Accessory / Separate Part Categor	Connection accessory	
Lines Description	3L + N	
Length In 18 Mm Modules	57	

### Complementary

Number Of Ways	38 ways Aux + N + L	
Poles Configuration For 1 Way	1 x 1P	
Connection Pitch	0.71 in (18 mm)	
Connector Type	tooth	
Distance Between Way	1.06 in (27 mm)	
Marking	L1L2L3	
Insulation	Insulated	
Device Presentation	Cuttable	
Provided Equipment	Set of 10 end piece	
[le] Rated Operational Current	100 A 104 °F (40 °C)	
[Ue] Rated Operational Voltage	415 V AC	
[Ui] Rated Insulation Voltage	500 V AC IEC 61439-2	
Mounting Location	Top or bottom tunnel type terminals Top or bottom double terminal	
9 Mm Pitches	114	
Width	39.37 in (1000 mm)	
Color	White RAL 9003)	
Range Compatibility	Acti 9 Acti9 iC60 Acti 9 Acti9 iK60 Acti 9 Acti9 iID Acti 9 Acti9 iID K Acti 9 Acti9 iSW Acti 9 Acti9 iSW	

### **Environment**

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Multi9 Multi9 C60



Standards	IEC 60947-7-1 IEC 61439-2
Fire Resistance	1760 °F (960 °C) 30 s ) IEC 60695-2-1
Pollution Degree	3 IEC 60947-7-1
Ip Degree Of Protection	IP20 with end-pieces and tooth covers

# Ordering and shipping details

Gtin 3606480485206

## **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	0.20 in (0.520 cm)	
Package 1 Width	0.35 in (0.900 cm)	
Package 1 Length	41.73 in (106.000 cm)	
Package 1 Weight	18.52 oz (525.000 g)	
Unit Type Of Package 2	P12	
Number Of Units In Package 2	135	
Package 2 Height	19.69 in (50.000 cm)	
Package 2 Width	47.24 in (120.000 cm)	
Package 2 Length	31.50 in (80.000 cm)	
Package 2 Weight	e 2 Weight 195.27 lb(US) (88.572 kg)	

### **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Reach Free Of Svhc	
<b>Ø</b>	Toxic Heavy Metal Free	
<b>Ø</b>	Mercury Free	
<b>Ø</b>	Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations