Product data sheet

Specifications



End tap box, I-Line Busway, max 2500A rated, aluminum, bolt connection, 4 wire

AF2525GETBMB

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 17,777.80 USD

| Μ | а | i | r | 1 |
|-----|---|---|---|---|
| 141 | a | l | I | l |

| Product | End tap box |
|---------|-------------|
| Range | I-Line |

Complementary

| Rated Current | 2500 A aluminium |
|---------------------------|---|
| Rated Operational Voltage | 600 V AC/DC 50/60 Hz |
| Length | 39.38 in (1000.25 mm) |
| Height | 28 in (711.20 mm) |
| Width | 20.88 in (530.35 mm) |
| Material | Aluminium: busbar |
| I-Line Value End | Bolt |
| Number Of Phases | 3 phase |
| For Use With | Busbar trunking 2500 A aluminium |
| Protection Type | 50 percent capacity integral ground bus |
| Wiring Configuration | 4-wire |
| | |

Environment

Standards UL 857 CSA C22.2 No 27:1994 IEC 61439-6

Ordering and shipping details

| Category | US10PE820014 |
|-------------------|--------------|
| Discount Schedule | 0PE8 |
| Gtin | 785901171553 |
| Returnability | Yes |
| Country Of Origin | US |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|--------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 27.99 in (71.1 cm) |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

| Package 1 Width | 20.87 in (53.0 cm) |
|------------------|---------------------------|
| Package 1 Length | 49.88 in (126.7 cm) |
| Package 1 Weight | 205.00 lb(US) (92.986 kg) |

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|--|
| Eu Rohs Directive | Compliant |
| | EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration |
| | Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |