


# Product data sheet

Specifications

## Cable duct - 25 x 25 mm - without cover - grey



AK2GD2525

 **Discontinued on:** Apr 19, 2023

**Product availability:** Non-Stock - Not normally stocked in distribution facility

 **Discontinued**

### Main

Product Or Component Type	Cable duct
Accessory / Separate Part Category	Cabling accessories
Range Compatibility	Spacial S3D Spacial CRN Thalassa PLA Thalassa PLS Thalassa PLM
Device Composition	Without cover
Quantity Per Set	Set of 8

### Complementary

Color	Gray RAL 7030)
Fixing Mode	Clip-on support By screws
Material	PVC (polyvinyl chloride)
Height	0.98 in (25 mm)
Length	78.74 in (2000 mm)
Width	0.98 in (25 mm)
Net Weight	0.57 lb(US) (0.26 kg)
Total Number Of Wires	25

### Environment

Ambient Air Temperature For Operation	23...140 °F (-5...60 °C)
Flame Retardance	V-0 UL 94
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1/1
Standards	VDE 0660 VDE 0506 DIN 43659

### Ordering and shipping details

Category	US1CP1018403
Discount Schedule	CP10
Gtin	3389110570335
Returnability	No

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Country Of Origin	FR
-------------------	----

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.79 in (2.000 cm)
Package 1 Width	0.98 in (2.500 cm)
Package 1 Length	78.74 in (200.000 cm)
Package 1 Weight	7.30 oz (207.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	1.77 in (4.500 cm)
Package 2 Width	2.17 in (5.500 cm)
Package 2 Length	78.94 in (200.500 cm)
Package 2 Weight	4.14 lb(US) (1.877 kg)
Unit Type Of Package 3	P2M
Number Of Units In Package 3	176
Package 3 Height	17.72 in (45.000 cm)
Package 3 Width	78.74 in (200.000 cm)
Package 3 Length	47.24 in (120.000 cm)
Package 3 Weight	113.39 lb(US) (51.432 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)