

Product data sheet

Specifications



Mounting plate, Linergy HK, 2P, 25A, 4.4mm², 105x54x61mm

AK5PA211PH12

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 96.00 USD

Main

Range	Linergy
Product Name	HK
Product Or Component Type	Mounting plate
Poles Description	2P
[Ith] Conventional Free Air Thermal Current	25 A
I ² T On Activation	200000 A².s
Number Of Cables	2 0.01 in² (4 mm²) 221 °F (105 °C)
Width	2.13 in (54 mm)
Height	4.13 in (105 mm)
Depth	2.40 in (61 mm)

Complementary

[UI] Rated Insulation Voltage	690 V IEC 60439-1
9 Mm Pitches	6
Net Weight	0.30 lb(US) (0.135 kg)

Environment

Standards	IEC 60439
Product Certifications	UL CSA DNV LROS (Lloyds register of shipping)

Ordering and shipping details

Category	US10I1122623
Discount Schedule	0I11
Gtin	3389110537437
Returnability	No
Country Of Origin	FR

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	2.48 in (6.3 cm)
Package 1 Width	2.87 in (7.3 cm)
Package 1 Length	4.72 in (12.0 cm)
Package 1 Weight	8.29 oz (235.0 g)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.