# Product data sheet

Specifications





# Mounting plate, Linergy HK, 3P+N, 25A, 4.4mm<sup>2</sup>, 190x54x61mm

AK5PA242

#### Main

Range	Linergy
Product Name	НК
Product Or Component Type	Mounting plate
Poles Description	3P + N
[Ith] Conventional Free Air Thermal Current	25 A
I <sup>2</sup> T On Activation	200000 A <sup>2</sup> .s
Number Of Cables	4 0.01 in² (4 mm²) 221 °F (105 °C)
Width	2.13 in (54 mm)
Height	7.48 in (190 mm)
Depth	2.40 in (61 mm)

#### Complementary

[Ui] Rated Insulation Voltage	690 V IEC 60439-1
9 Mm Pitches	6
Net Weight	0.51 lb(US) (0.23 kg)

#### Environment

Standards	IEC 60439
Product Certifications	UL LROS (Lloyds register of shipping) CSA DNV

#### Ordering and shipping details

Category	22623-PANEL BUS (AK5)	
Discount Schedule	111	
Gtin	3389110356809	
Returnability	No	

#### **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Height	2.48 in (6.3 cm)
Package 1 Width	2.95 in (7.5 cm)
Package 1 Length	8.66 in (22.0 cm)
Package 1 Weight	13.58 oz (385.0 g)
Unit Type Of Package 2	\$03
Number Of Units In Package 2	20
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	18.60 lb(US) (8.437 kg)

## **Contractual warranty**

Warranty

18 months

### Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations