Product data sheet

Specifications





Plug outlet, Linergy HK, 2P, 32A, 1 points, 4 mm², cable length 1000

AK5PC32LPH

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 42.15 USD

Main

Range	Linergy
Product Name	нк
Product Or Component Type	Plug outlet
Poles Description	2P
[Ith] Conventional Free Air Thermal Current	32 A
I ² T On Activation	200000 A².s
Number Of Points	1
Number Of Cables	2 0.01 in² (4 mm²)
Cable Length	3.28 ft (1 m)
Quantity Per Set	Set of 6

Complementary

[Ui] Rated Insulation Voltage	600 V CSA 600 V UL 690 V IEC 60439-1
Peak Current	25 kA
Width	0.71 in (18 mm)
Height	1.81 in (46 mm)
Depth	1.50 in (38 mm)
Net Weight	0.09 lb(US) (0.04 kg)

Environment

Standards	IEC 60439
Product Certifications	UL DNV LROS (Lloyds register of shipping)

Ordering and shipping details

Category	US10l1122623
Discount Schedule	0111
Gtin	3389110588996
Returnability	No
Country Of Origin	FR

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.39 in (8.6 cm)
Package 1 Width	8.74 in (22.2 cm)
Package 1 Length	9.06 in (23 cm)
Package 1 Weight	4.20 oz (119 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	3.39 in (8.6 cm)
Package 2 Width	8.74 in (22.2 cm)
Package 2 Length	9.06 in (23 cm)
Package 2 Weight	25.33 oz (718 g)
Unit Type Of Package 3	S04
Number Of Units In Package 3	54
Package 3 Height	11.81 in (30 cm)
Package 3 Width	15.75 in (40 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	17.29 lb(US) (7.844 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations