Product data sheet

Specifications





Plug outlet, Linergy HK, 3P, 32A, 2 points, 4 mm², cable length 1000mm

AK5PC33L

Product availability: Stock - Normally stocked in distribution

Price*: 37.80 USD

Main

Range	Linergy	
Product Name	нк	
Product Or Component Type	Plug outlet	
Poles Description	3P	
[Ith] Conventional Free Air Thermal Current	32 A	
I ² T On Activation	200000 A².s	
Number Of Points	2	
Number Of Cables	3 0.01 in² (4 mm²)	
Cable Length	3.28 ft (1 m)	
Quantity Per Set	Set of 6	

Complementary

[Ui] Rated Insulation Voltage	600 V CSA 600 V UL 690 V IEC 60439-1
Peak Current	25 kA
Width	1.42 in (36 mm)
Height	1.81 in (46 mm)
Depth	1.50 in (38 mm)

Environment

Standards	IEC 60439
Product Certifications	UL DNV
	LROS (Lloyds register of shipping)
	CSA

Ordering and shipping details

Category	US10I1122623	
Discount Schedule	0111	
Gtin	3389110576863	
Returnability	No	
Country Of Origin	FR	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.43 in (8.700 cm)
Package 1 Width	9.25 in (23.500 cm)
Package 1 Length	9.21 in (23.400 cm)
Package 1 Weight	5.29 oz (150.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	3.43 in (8.700 cm)
Package 2 Width	9.25 in (23.500 cm)
Package 2 Length	9.21 in (23.400 cm)
Package 2 Weight	34.92 oz (990.000 g)
Unit Type Of Package 3	S04
Number Of Units In Package 3	54
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	15.75 in (40.000 cm)
Package 3 Length	23.62 in (60.000 cm)
Package 3 Weight	21.61 lb(US) (9.800 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
②	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov