

Product data sheet

Specifications

PREFORMED FIXING RAIL

AM1EC200



Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 118.00 USD

Main

Accessory / Separate Part Category	Mounting accessories
Accessory / Separate Part Type	Notched uprights
Enclosure Accessory Description	Notched mounting rail
Quantity Per Set	Set of 2 Set of 4
Star-Delta Starter Component	Uprights Mounting rails

Complementary

Assembly Style	For assembly
Depth	0.98 in (25 mm)
Height	78.74 in (2000 mm) 0.00 in (0 mm)
Horizontal Fixing Centres	61.02 in (1550 mm)
Length	78.74 in (2000 mm)
Material	Steel coated with zinc chromate
Motor Power Kw	110 kW 160 kW 185 kW 375 kW 100 kW 220 kW 90 kW 200 kW 250 kW 280 kW 315 kW
Motor Starter Type	Star-delta starters
Number Of Devices	1 2
Product Compatibility	For enclosure of width 1600 mm For enclosure of height 1600 mm
Net Weight	5.29 lb(US) (2.4 kg) 6.57 lb(US) (2.98 kg)
Type Of Rail	Notched
Surface Treatment	Zinc chromate
Thickness	0.08 in (2 mm)
Vertical Fixing Centres	59.06 in (1500 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	0.00 in (0 mm) 62.99 in (1600 mm) 1.57 in (40 mm)
-------	---

Ordering and shipping details

Category	US1000I22621
Discount Schedule	000I
Gtin	3389110542141
Returnability	No
Country Of Origin	IT

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.49 in (1.25 cm)
Package 1 Width	1.97 in (5 cm)
Package 1 Length	78.74 in (200 cm)
Package 1 Weight	6.50 lb(US) (2.95 kg)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	2
Package 2 Height	78.74 in (200 cm)
Package 2 Width	1.97 in (5 cm)
Package 2 Length	0.98 in (2.5 cm)
Package 2 Weight	13.01 lb(US) (5.9 kg)
Unit Type Of Package 3	P2M
Number Of Units In Package 3	160
Package 3 Height	19.29 in (49 cm)
Package 3 Width	78.74 in (200 cm)
Package 3 Length	47.24 in (120 cm)
Package 3 Weight	1558.67 lb(US) (707 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)