





Straight length, I-Line Busway, 2000A, 600VAC, 3 phase, 3 wire, integral ground bus, Al, plug-in, 4ft

AP2320G4ST

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 7,927.58 USD

### Main

| Range Of Product          | I-Line          |
|---------------------------|-----------------|
| Product Or Component Type | Straight length |
| Application               | Plua-in         |

## Complementary

| Line Rated Current                            | 2000 A                                  |
|---|---|
| Short Circuit Rating                          | 125 kA                                  |
| Busbar Material                               | Aluminium: busbar                       |
| Integral Ground/High Short<br>Circuit Bracing | 50 percent capacity integral ground bus |
| Rated Voltage                                 | 600 V AC                                |
| Number Of Phases                              | 3 phase                                 |
| Wiring Configuration                          | 3-wire                                  |
| Length  | 4 ft (1.22 m)                           |

#### **Environment**

| Product Certifications | UL listed file E22182                         |
|------------------------|---|
| Standards              | CSA C22.2 No 27:1997<br>IEC 61439-2<br>UL 857 |

# Ordering and shipping details

| Category          | US10PE820331 |
|-------------------|--------------|
| Discount Schedule | 0PE8         |
| Gtin              | 785901329909 |
| Returnability     | No           |
| Country Of Origin | US           |

## **Packing Units**

| Unit Type Of Package 1       | PCE                       |
|------------------------------|---------------------------|
| Number Of Units In Package 1 | 1                         |
| Package 1 Weight             | 98 20 lb/LIS) (44 543 kg) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

# **Contractual warranty**

Warranty

18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

| <b>⊘</b> | Reach Free Of Svhc             |
|----------|--------------------------------|
| <b>⊘</b> | Toxic Heavy Metal Free         |
| <b>⊘</b> | Mercury Free                   |
| <b>⊘</b> | Rohs Exemption Information Yes |
| <b>⊘</b> | Pvc Free                       |

#### **Certifications & Standards**

**Reach Regulation** 

| Eu Rohs Directive         | Compliant   |
|---------------------------|---|
| Eu Rons Directive         | '   |
|                           | EU RoHS Declaration   |
| China Rohs Regulation     | China RoHS declaration  |
|                           | Pro-active China RoHS declaration (out of China RoHS legal scope)   |
| Environmental Disclosure  | Product Environmental Profile   |
| Circularity Profile       | No need of specific recycling operations  |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

**REACh Declaration**