

Product data sheet

Specifications



Rack PDU, Switched, 1U, 15A, 100/120V, (8)5-15



AP7900B

Product availability: Stock - Normally stocked in distribution facility

Overview

Presentation This APC Switched Rack PDU power distribution unit has a wide range of standardized PDU features that increase network efficiency, manageability and functionality. The output and input connections are (8)5-15. Network management capabilities allow you to configure and manage rack PDUs from remote locations. It has a local current monitoring display that gives a visible warning in case of an overload. The remote individual outlet control provides real-time monitoring of connected loads. It has a multi-tier user access that enables you to restrict unauthorized use of outlets. This rack has a single input power source making it easy to install.

Lead Time Usually in Stock

Main

Color Black

Product Or Component Type PDU

Pdu Type Switched

Cord Length 12 ft (3.66 m)

Number Of Cables 1

Provided Equipment Cord retention bracket(s)
Horizontal mounting brackets
User Manual
Installation guide

Complementary

Input Voltage 100 V
120 V

Height 1.73 in (4.4 cm)

Width 17.52 in (44.5 cm)

Output Voltage 120 V

Depth 4.25 in (10.8 cm)

Net Weight 5.00 lb(US) (2.27 kg)

Mounting Location Front
Rear

Mounting Preference No preference

Input Plug Type NEMA 5-15P

Mounting Mode Rack-mounted

Rack Units 1U

Mounting Position Horizontal

Line Rated Current 12 A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Acceptable Input Voltage	100...120 V
Input Current Limits	15 A
Load Capacity	1440 VA
Input Frequency	50/60 Hz
Outlet Type And Quantity	8 NEMA 5-15R

Environment

Product Certifications	cUL Listed UL Listed
Standards	FCC Part 15 class A ICES-003
Ambient Air Temperature For Operation	32...113 °F (0...45 °C)
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	0...95 %
Storage Altitude	0...50000 ft (0.00...15240.00 m)

Ordering and shipping details

Category	80230-IG SEBA TO SEUSA
Discount Schedule	BMS1
Gtin	731304331568
Returnability	No
Country Of Origin	PH

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.76 in (7 cm)
Package 1 Width	13.50 in (34.3 cm)
Package 1 Length	18.50 in (47 cm)
Package 1 Weight	7.61 lb(US) (3.45 kg)

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

California Proposition 65 WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov