Product data sheet

Specifications





Power Cord Kit (6 ea), Locking, C19 to C20 (90 Degree), 0.6m

AP8712R

Overview

Presentation	Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
Lead Time	Usually in Stock

Main

Input Connection Type	IEC 60320 C20
Cable Length	2 ft (0.61 m)
Number Of Cables	6
Provided Equipment	Left-angle jumper cords Right-angle jumper cords

Physical

Color	Black
Height	11.81 in (30 cm)
Width	2.36 in (6 cm)
Depth	2.36 in (6 cm)
Net Weight	2.47 lb(US) (1.12 kg)
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Max Line Current	16 A	
Input Current Limits	16 A	

Output

Maximum Total Current Draw Per Phase	16 A
Number Of Power Socket Outlets	1 IEC 60320 C19
Cord Length	2 ft (0 61 m)

Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Product Certifications	CCC	
	CSA	
	PSE	
	UL Listed	
	VDE	

Environmental

Ambient Air Temperature For Operation	32167 °F (075 °C)
Relative Humidity	2080 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-13167 °F (-2575 °C)
Storage Relative Humidity	2080 %
Storage Altitude	050000 ft (0.0015240.00 m)

Ordering and shipping details

Gtin	731304279679

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.81 in (30 cm)
Package 1 Width	2.36 in (6 cm)
Package 1 Length	2.36 in (6 cm)
Package 1 Weight	2.47 lb(US) (1.12 kg)
Unit Type Of Package 2	CAR
Number Of Units In Package 2	13
Package 2 Height	10.24 in (26 cm)
Package 2 Width	13.31 in (33.8 cm)
Package 2 Length	22.24 in (56.5 cm)
Package 2 Weight	33.07 lb(US) (15 kg)
Unit Type Of Package 3	PAL
Number Of Units In Package 3	13
Package 3 Height	56.69 in (143.99 cm)
Package 3 Width	39.37 in (100 cm)
Package 3 Length	47.24 in (120 cm)
Package 3 Weight	33.07 lb(US) (15 kg)
Scc14	10731304279676

Contractual warranty

Warranty	2	vears repair or replace



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >







Take-back Transparency RoHS/REACh

Resource performance



Take-Back Program Available

Well-being performance



Lead Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov