# Product data sheet

Specifications





# Power Cord Kit (6 ea), Locking, C19 to C20, 0.6m

AP8712S

Overview	
Presentation	Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.
Lead Time	Usually in Stock
Main	
Input Connection Type	IEC 60320 C20
Cable Length	2 ft (0.61 m)
Number Of Cables	6
Physical	
Color	Black
Height	11.81 in (30 cm)
Width	2.36 in (6 cm)
Depth	2.56 in (6.5 cm)
Net Weight	2.47 lb(US) (1.12 kg)
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Input	
Max Line Current	16 A
Input Current Limits	16 A
Output	
Maximum Total Current Draw Per Phase	16 A
Number Of Power Socket Outlets	1 IEC 60320 C19
Cord Length	2 ft (0.61 m)
Conformance	
Product Certifications	CCC CSA

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

PSE UL Listed VDE

## Environmental

Ambient Air Temperature For Operation	32167 °F (075 °C)
Relative Humidity	2080 %
Operating Altitude	010000 ft
Ambient Air Temperature For Storage	-13167 °F (-2575 °C)
Storage Relative Humidity	2080 %
Storage Altitude	050000 ft (0.0015240.00 m)

### Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
Gtin	731304279686
Returnability	No
Country Of Origin	CN

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.81 in (30 cm)
Package 1 Width	2.36 in (6 cm)
Package 1 Length	2.56 in (6.5 cm)
Package 1 Weight	2.47 lb(US) (1.12 kg)
Scc14	10731304279683

#### **Contractual warranty**

Warranty

2 years repair or replace

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Take-back Transparency RoHS/REACh

#### **Resource performance**

Take-Back Program Available

#### Well-being performance

Lead Free

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov