

Product data sheet

Specifications



NetShelter SV 42U 600mm Wide x 1060mm Deep Enclosure with Sides, Black, Single Rack Unassembled

AR2400FP1

Overview

Presentation	Not all installation sites have space clearance required to move and install standard height enclosures. This unassembled Universal IT enclosure option for low to medium density server and networking applications is packaged for transport through narrow spaces and assembly at the installation site.
Lead Time	Usually in Stock

Main

Product Or Component Type	Rack enclosure
Number Of Rack Unit	42U
Provided Equipment	Adjustable vertical mounting rails Baying hardware Casters Door handle Doors Installation guide Key(s) Keyed-alike doors and side panels Leveling feet Mounting Hardware Pre-installed casters 2 x Plate 4 x Bolt down brackets Roof Side Panels Side Panel Lock Slam Latches

Physical

Height	80.98 in (205.7 cm)
Width	23.62 in (60 cm)
Depth	41.73 in (106 cm)
Net Weight	247.36 lb(US) (112.2 kg)
Color	Black
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Maximum Mounting Depth	30.60 in (77.72 cm)
Minimum Mounting Depth	6.60 in (16.76 cm)
Rack Width	19"

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Marking	14 gauge EIA mounting rail 16 gauge front door 18 gauge post 16 gauge rear door 19 gauge roof 18 gauge side panels
Permanent Permissible Load	1014 lb(US) (459.94 kg) dynamic 2205 lb(US) (1000.17 kg) static

Conformance

Standards	UL 2416 UL 60950-1 EIA-310E
-----------	-----------------------------------

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
Gtin	731304302049
Returnability	No
Country Of Origin	CN

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	31.89 in (81 cm)
Package 1 Width	26.89 in (68.3 cm)
Package 1 Length	87.80 in (223 cm)
Package 1 Weight	486.46 lb(US) (220.656 kg)

Contractual warranty

Warranty	5 year repair or replace
----------	--------------------------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)





Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 Reach Free Of Svhc

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure [Product Environmental Profile](#)