Product data sheet

Specification





Circuit breaker, PowerPacT B, 80A, 3 pole, 600Y/347VAC, 14kA, lugs, thermal magnetic, 80%, control wire ON end

BDL36080LU

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 1,306.00 USD

Main

Range	PowerPact	
Product Name	PowerPact B	
Device Short Name	BD 080	
Product Or Component Type	Circuit breaker	
Device Application	Distribution	

Complementary

Line Rated Current	80 A
Number Of Poles	3P
Protected Poles Description	3t
Control Type	Toggle
Breaking Capacity Code	D
Breaking Capacity	25 kA 208Y/120 V AC 50/60 Hz UL 489 18 kA 240 V AC 50/60 Hz UL 489 Icu 25 kA 480/277 V AC 50/60 Hz UL 489 Icu 14 kA 480 V AC 50/60 Hz UL 489 18 kA 600Y/347 V AC 50/60 Hz UL 489 14 kA 250 V DC UL 489 25 kA Icu 18 kA
[Ue] Rated Operational Voltage	525 V AC 50/60 Hz UL 489
Network Frequency	50/60 Hz
[Ics] Rated Service Breaking Capacity	25 kA 220240 V AC 50/60 Hz IEC 60947-2 14 kA 500525 V AC 50/60 Hz IEC 60947-2 18 kA 380415 V AC 50/60 Hz IEC 60947-2 18 kA 440 V AC 50/60 Hz IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV IEC 60947-2
Trip Unit Technology	Thermal-magneticTM-D,
Continuous Current Rating	80 %
[Ui] Rated Insulation Voltage	800 V IEC 60947-2
Trip Unit Name	TM-D
Suitability For Isolation	Yes IEC 60947-2
Utilisation Category	Category A

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Mechanical Durability	15000 cycles IEC 947-1 Annex K ed 5.2	
Electrical Durability	10000 cycles IEC 947-1 Annex K ed 5.2 440 V In	
Connection Pitch	1.06 in (27 mm)	
Awg Gauge	AWG 6AWG 2/0 fine stranded aluminium/copper AWG 14AWG 3/0 rigid or stranded aluminium/copper	
Local Signalling	Presence of auxiliary contacts flag green)	
Mounting Mode	Clip-on 35 mm symmetrical DIN rail) By screws plate)	
Electrical Connection	Everlink lug, line Everlink lug, load	
Tightening Torque	44.25 lbf.in (5 N.m) 0.000.02 in² (2.516 mm²) (AWG 14AWG 4) 79.66 lbf.in (9 N.m) 0.040.15 in² (2595 mm²) (AWG 3AWG 3/0)	
Number Of Slots	1 auxiliary switch OF plug-in) 1 voltage release MN or MX plug-in) 1 alarm switch SD plug-in)	
Power Wire Stripping Length	0.79 in (20 mm)	
Color	Gray RAL 7016)	
9 Mm Pitches	9	
Height	5.39 in (137 mm)	
Width	3.19 in (81 mm)	
Depth	3.15 in (80 mm)	
Net Weight	2.37 lb(US) (1.074 kg)	
Quantity Per Set	Set of 1	
Circuit Breaker Application	HACR rated	

Environment

Quality Labels	CE
Standards	UL 489 CSA C22.2 No 5 GB 14048.2 EN/IEC 60947-2 EN/IEC 60947-5-1 NMX J-266 NEMA AB1
Product Certifications	UL IEC CCC EAC CSA NOM
Ip Degree Of Protection	Front cover IP40 IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Pollution Degree	3 IEC 60947-1
Ambient Air Temperature For Operation	-13158 °F (-2570 °C)
Ambient Air Temperature For Storage	-58185 °F (-5085 °C)
Operating Altitude	6561.68 ft (2000 m) without derating 5000 m with derating

Ordering and shipping details

Category US10DE201130

Discount Schedule	0DE2	
Gtin	3606481149152	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.70 in (11.938 cm)
Package 1 Width	3.30 in (8.382 cm)
Package 1 Length	8.10 in (20.574 cm)
Package 1 Weight	2.60 lb(US) (1.179 kg)
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	18.74 lb(US) (8.5 kg)

Sustainability Screen Premium*

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

Ø	Mercury Free
Ø	Rohs Exemption Information Yes
⊘	Pvc Free
⊘	Halogen Free Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov