

Product data sheet

Specifications



Panelboard, I-Line, 400A, 1 phase,
400A NQ lighting section with 42
circuits, Cu bus

CP118864N4Q4C

Discontinued on: Jan 31, 2024

Discontinued

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Range	I-Line
Product Type	Panelboard
Lighting Section Type	NQ
Provided Equipment	Neutral bar copper)
Circuit Breaker Type	QJ LL HD/HG/HJ/HL LI Q4 QG QB FC PK LG FA LJ LD JD/JG/JJ/JL QO LA/LH QOB QD

Complementary

Rated Current	400 A
Lighting Section Current	400 A
Rated Operational Voltage	600Y/347 V AC 48 V DC
Breaking Capacity	10...200 kA main 3...200 kA branch
Main Type	Main lugs Main breaker
Lighting Section Number Of Circuits	42
Number Of Phases	1 phase
Height	86 in (2184.40 mm)
Width	26 in (660.40 mm)
Depth	9.5 in (241.30 mm)

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Nema Rating	NEMA 2 NEMA 1/3R/4/4X/12
Certifications	UL Listed cULus CE

Ordering and shipping details

Category	US1PE1A08310
Discount Schedule	PE1A
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	800.00 lb(US) (362.874 kg)

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation