


Product data sheet

Specifications



Operating mechanism, disconnect switch, 30 A, 600 VAC, NEMA Size 0 and 1

D10S1

 Discontinued on: Jun 2, 2021

 Discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	D10S
Product	Disconnect Switch
Current Rating	30 A
Horsepower Rating	5 hp 120 V AC 10 hp 200/240 V AC 20 hp 480 V AC 25 hp 600 V AC
Voltage Rating	600 V AC
Mounting Type	Door
Nema Size	0 1
Service Entrance Rated	Not service entrance rated

Ordering and shipping details

Category	US1000T22642
Discount Schedule	000T
Gtin	785901118558
Returnability	No
Country Of Origin	MX

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Eu Rohs Directive	Not compliant
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov