





Safety switch, general duty, fusible, 400A, 3 pole, 125hp, 240VAC, NEMA 1, neutral factory installed

D325N

Product availability: Stock - Normally stocked in distribution facility

Price*: 3,113.00 USD

Main

| Product | Single Throw Safety Switch | |
|---------------------------|---|--|
| Duty Rating | General duty | |
| Device Application | Residential | |
| Disconnect Type | Fusible disconnect switch | |
| Factory Installed Neutral | Neutral (factory installed) | |
| Phase | 3 phase | |
| Number Of Poles | 3 | |
| Current Rating | 400 A | |
| Voltage Rating | 240 V AC | |
| Enclosure Rating Nema | NEMA 1 | |
| Motor Power Hp | 50 hp at 240 V AC 60 Hz for 3 phase motors 125 hp at 240 V AC 60 Hz for 3 phase motors | |

Complementary

Environment

Certifications

| Short Circuit Current Rating | 100 kA maximum depending on fuse H, K, J or R |
|------------------------------|--|
| Fuse Type | H, K, J or R |
| Mounting Type | Surface |
| Electrical Connection | Lugs |
| Wiring Configuration | 4-wire (3PH + G) |
| Wire Size | AWG 1/0600 kcmil aluminium/copper 2 x AWG 1/02 x 300 kcmil aluminium/copper |
| Tightening Torque | 340 lbf.in (38.41 N.m) (AWG 1/0750 kcmil) 340 lbf.in (38.41 N.m) (2 x AWG 1/02 x 300 kcmil) |
| Depth | 8.88 in (225.55 mm) |
| Width | 24.88 in (631.95 mm) |
| Height | 45.12 in (1146.05 mm) |
| Net Weight | 114.64 lb(US) (52 kg) |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

UL listed file E2875

Ordering and shipping details

| Category | US1DE1A00007 |
|-------------------|--------------|
| Discount Schedule | DE1A |
| Gtin | 785901461555 |
| Returnability | Yes |
| Country Of Origin | MX |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|---------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 11.30 in (28.7 cm) |
| Package 1 Width | 25.98 in (66.0 cm) |
| Package 1 Length | 47.99 in (121.9 cm) |
| Package 1 Weight | 115.00 lb(US) (52.163 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

| | Mercury Free |
|----------|------------------------------------|
| | Rohs Exemption Information Yes |
| ② | Pvc Free |
| ⊘ | Halogen Free Plastic Parts Product |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |