Product data sheet

Specifications





Fuse carrier, TeSys DF, 1P+N, 32A, 690VAC, fuse size 10x38 mm

DF101N

Product availability: Stock - Normally stocked in distribution facility

Price*: 23.00 USD

Main

Range	TeSys
Product Name	TeSys DF
Product Or Component Type	Fuse carrier
Device Short Name	DF10
Device Composition	tubular link locked in Neutral pole
Product Compatibility	DF2CA fuse cartridge DF2CN fuse cartridge
Poles Description	1P + N
Fuse Size	10 x 38 mm
Fuse Type	, aM , gG
Control Type	Toggle padlockable
Utilisation Category	AC-20B IEC 60947-3 DC-20B IEC 60947-3
[Ue] Rated Operational Voltage	690 V AC 690 V DC
[le] Rated Operational Current	32 A 400 V AC
[Ith] Conventional Free Air Thermal Current	32 A 68 °F (20 °C)
[Ui] Rated Insulation Voltage	690 V AC
[Uimp] Rated Impulse Withstand Voltage	6 kV
Overvoltage Category	W
Short-Circuit Withstand	120 kA 400 V IEC 60947-3 120 kA 500 V IEC 60947-3
Power Dissipation In W	3 W maximum power dissipation by fuse

Complementary

Standards	EN/IEC 60947-3 EN/IEC 60269-2 UL 4248-1 CSA C22.2 No 4248-1 EN 45545-2: R22 HL2
Product Certifications	IEC UL Recognized CSA CCC EAC DNV-GL

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Mounting Support	35 mm symmetrical DIN rail
Mounting Position	Vertical +/- 23°)
Connections - Terminals	screw clamp terminals 1 0.000.02 in ² (116 mm ²)rigid screw clamp terminals 2 0.000.01 in ² (16 mm ²)rigid screw clamp terminals 1 0.000.02 in ² (116 mm ²)flexible with or without screw clamp terminals 2 0.000.01 in ² (16 mm ²)flexible with or without
Tightening Torque	19.47 lbf.in (2.2 N.m) PZ2 19.47 lbf.in (2.2 N.m) flat Ø 5.5 mm
Height	3.13 in (79.5 mm)
Width	1.38 in (35 mm)
Depth	2.40 in (61 mm)
Net Weight	0.19 lb(US) (0.087 kg)
Quantity Per Set	Set of 6

Environment

Ambient Air Temperature For Storage	-40158 °F (-4070 °C)
Ambient Air Temperature For Operation	-40158 °F (-4070 °C) with derating above 20°C
Operating Altitude	06561.68 ft (02000 m)
Ip Degree Of Protection	IP20
Pollution Degree	3
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility Code	DF10

Ordering and shipping details

Category	US10CP121714
Discount Schedule	0CP1
Gtin	3389119407229
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.38 in (3.5 cm)
Package 1 Width	2.44 in (6.2 cm)
Package 1 Length	3.15 in (8 cm)
Package 1 Weight	3.25 oz (92 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	2.68 in (6.8 cm)
Package 2 Width	3.35 in (8.5 cm)
Package 2 Length	8.74 in (22.2 cm)
Package 2 Weight	20.60 oz (584 g)

Unit Type Of Package 3	S03
Number Of Units In Package 3	96
Package 3 Height	11.81 in (30 cm)
Package 3 Width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)
Package 3 Weight	21.79 lb(US) (9.885 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
	Circularity Profile
California Proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov