## Product data sheet

Specifications





# Fuse carrier, TeSys DF, 1P, 50A, 690VAC, fuse size 14x51mm, blown fuse indicator

DF141V

Product availability: Non-Stock - Not normally stocked in distribution facility

#### Price\*: 30.00 USD

#### Main

Range	TeSys
Product Name	TeSys DF
Product Or Component Type	Fuse carrier
Device Short Name	DF14
Product Compatibility	DF2EA fuse cartridge DF2EN fuse cartridge
Poles Description	1P
Fuse Size	14 x 51 mm
Fuse Type	, aM , gG
Control Type	Toggle
Local Signalling	Blown fuse indication
[Ue] Rated Operational Voltage	690 V AC 690 V DC
[le] Rated Operational Current	50 A
[Ui] Rated Insulation Voltage	690 V AC
[Uimp] Rated Impulse Withstand Voltage	8 kV
[Ipk] Rated Peak Withstand Current	15 kA with tubular links IEC 60269-1
Short-Circuit Withstand	120 kA 400 V IEC 60947-3 120 kA 500 V IEC 60947-3 80 kA 690 V IEC 60947-3

### Complementary

Standards	EN/IEC 60947-3 EN/IEC 60269-2 UL 4248-1 CSA C22.2 No 4248-1
Product Certifications	IEC UL Recognized CSA EAC
Mounting Support	35 mm symmetrical DIN rail
Mounting Position	Vertical +/- 23°)

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Connections - Terminals	screw clamp terminals 1 0.000.04 in² (2.525 mm²)rigid screw clamp terminals 2 0.000.02 in² (2.510 mm²)rigid screw clamp terminals 1 0.000.04 in² (2.525 mm²)flexible with or without screw clamp terminals 2 0.000.02 in² (2.510 mm²)flexible with or without
Tightening Torque	30.98 lbf.in (3.5 N.m)
Height	4.36 in (110.8 mm)
Width	1.04 in (26.5 mm)
Depth	3.01 in (76.5 mm)
Net Weight	0.32 lb(US) (0.143 kg)
Quantity Per Set	Set of 6

## Environment

Ambient Air Temperature For Storage	-40176 °F (-4080 °C)
Ambient Air Temperature For Operation	-4140 °F (-2060 °C) with derating above 20°C
Ip Degree Of Protection	IP20 conforming to IEC 60529
Protective Treatment	ТН
Fire Resistance	1760 °F (960 °C) IEC 60695-2-1
Compatibility Code	DF14

## Ordering and shipping details

Category	US10CP121714
Discount Schedule	0CP1
Gtin	3389119407434
Returnability	No
Country Of Origin	FR

## **Packing Units**

•	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.37 in (11.100 cm)
Package 1 Width	1.04 in (2.650 cm)
Package 1 Length	3.03 in (7.700 cm)
Package 1 Weight	4.16 oz (118.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	6.46 in (16.400 cm)
Package 2 Width	4.45 in (11.300 cm)
Package 2 Length	3.11 in (7.900 cm)
Package 2 Weight	27.30 oz (774.000 g)
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	11.81 in (30.000 cm)

Package 3 Length

15.75 in (40.000 cm)

Package 3 Weight

21.29 lb(US) (9.655 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

$\checkmark$	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	No need of specific recycling operations
	Circularity Profile
California Proposition 65	WARNING: Cancer - www.P65Warnings.ca.gov