Product data sheet

Specifications



Green



Safety switch, general duty, non fusible, 60A, 3 pole, 3 wire, 15hp, 240VAC, NEMA 3R, bolt on hub provision

DU322RB

Product availability: Stock - Normally stocked in distribution facility

Price*: 443.00 USD

Main

Product	Single Throw Safety Switch
Duty Rating	General duty
Device Application	Residential
Disconnect Type	Non-fusible disconnect switch
Factory Installed Neutral	None
Phase	3 phase
Number Of Poles	3
Current Rating	60 A
Voltage Rating	240 V AC
Enclosure Rating Nema	NEMA 3R
Motor Power Hp	10 hp at 240 V AC 60 Hz for 1 phase motors 15 hp at 240 V AC 60 Hz for 3 phase motors

Complementary

Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	3-wire
Wire Size	AWG 12AWG 3 aluminium AWG 14AWG 3 copper
Tightening Torque	35 lbf.in (3.95 N.m) 0.000.01 in ² (2.085.26 mm ²) (AWG 14AWG 10) 35 lbf.in (3.95 N.m) (AWG 14AWG 10) 45 lbf.in (5.08 N.m) 0.01 in ² (8.37 mm ²) (AWG 8) 45 lbf.in (5.08 N.m) 0.020.03 in ² (12.321.12 mm ²) (AWG 6AWG 4) 50 lbf.in (5.65 N.m) 0.04 in ² (26.67 mm ²) (AWG 3)
Depth	3.75 in (95.25 mm)
Width	7.75 in (196.85 mm)
Height	9.63 in (244.60 mm)
Net Weight	26.01 lb(US) (11.8 kg)

Environment

Certifications

UL listed file E2875

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US1DE1A00106
Discount Schedule	DE1A
Gtin	785901491767
Returnability	Yes
Country Of Origin	US

Packing Units

PCE
1
5.30 in (13.462 cm)
7.80 in (19.812 cm)
9.80 in (24.892 cm)
4.85 lb(US) (2.2 kg)
PAL
120
36.00 in (91.44 cm)
40.00 in (101.6 cm)
48.00 in (121.92 cm)
660.00 lb(US) (299.371 kg)
CAR
5
10.70 in (27.178 cm)
10.40 in (26.416 cm)
23.80 in (60.452 cm)
25.70 lb(US) (11.657 kg)
· · · · ·

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov