Product data sheet





Cable end, Linergy TR cable ends, single conductor, brown, 10mmÂ2, medium size, 10 sets of 100

DZ5CA102

Product availability: Stock - Normally stocked in distribution

Price*: 0.72 USD

Main

| Range Of Product | Linergy |
|---------------------------|-------------------|
| Product Or Component Type | Cable end |
| Cable End Size | Medium |
| Standards | NF C 63-023 |
| Type Of Packing | Bag |
| Quantity Per Set | Set of 100 |
| Cable Cross Section | 0.02 in² (10 mm²) |

Complementary

| Cable End Type | Single conductor |
|------------------------|----------------------------------|
| Additional Information | For additional marker tag holder |
| Color | Brown |
| Bezel Material | Halogen-free plastic |
| Tube Material | Copper ISO 1337 |
| Number Of Cables | 1 |
| Awg Gauge | AWG 8 |
| Bezel Size | Ø 8.4 mm |
| Tube Diameter | 0.19 in (4.9 mm) |
| Length | 0.87 in (22 mm) |
| Tube Length | 0.47 in (12 mm) |
| Cad Overall Depth | 0.87 in (22 mm) |
| Net Weight | 0.13 lb(US) (0.057 kg) |

Environment

Ambient Air Temperature For -4...221 °F (-20...105 °C)

Ordering and shipping details

| Category | US1000I22621 |
|-------------------|---------------|
| Discount Schedule | 0001 |
| Gtin | 3389110535594 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| Returnability | Yes |
|-------------------|-----|
| Country Of Origin | MX |

Packing Units

| 9 | |
|------------------------------|------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 0.16 in (0.400 cm) |
| Package 1 Width | 0.16 in (0.400 cm) |
| Package 1 Length | 0.55 in (1.400 cm) |
| Package 1 Weight | 0.02 oz (0.500 g) |
| Unit Type Of Package 2 | BB1 |
| Number Of Units In Package 2 | 100 |
| Package 2 Height | 2.36 in (6.000 cm) |
| Package 2 Width | 0.79 in (2.000 cm) |
| Package 2 Length | 5.91 in (15.000 cm) |
| Package 2 Weight | 1.90 oz (54.000 g) |
| Unit Type Of Package 3 | S02 |
| Number Of Units In Package 3 | 6000 |
| Package 3 Height | 5.91 in (15.000 cm) |
| Package 3 Width | 11.81 in (30.000 cm) |
| Package 3 Length | 15.75 in (40.000 cm) |
| Package 3 Weight | 7.80 lb(US) (3.537 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

| ⊘ | Reach Free Of Svhc |
|----------|------------------------------------|
| Ø | Toxic Heavy Metal Free |
| Ø | Mercury Free |
| ② | Rohs Exemption Information Yes |
| ⊘ | Pvc Free |
| ② | Halogen Free Plastic Parts Product |

Certifications & Standards

| Reach Regulation | REACh Declaration |
|-----------------------|--|
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |
| Circularity Profile | No need of specific recycling operations |