# Product data sheet

Specifications



# Circuit breaker, FA, 600V, 80A, 3 pole

FA36080

#### Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

### Complementary

Line Rated Current	80 A
Number Of Poles	3P
Breaking Capacity Code	A
Mounting Mode	I-Line
Magnetic Hold Current	800 A
Magnetic Tripping Current	1450 A
Electrical Connection	Lugs, load I-Line connection, line
Terminal Identifier	AL50FA
Phase Connection	ABC
Height	6.4 in (162.56 mm)
Width	4.5 in (114.30 mm)
Depth	4.13 in (104.90 mm)
Circuit Breaker Application	HACR rated

# Environment

Certifications	CSA
	UL Listed

# Ordering and shipping details

Category	01010-FA/FH 600V	
Discount Schedule	DE2	
Gtin	00785901338758	
Returnability	No	
Country Of Origin	МХ	

#### **Packing Units**

Unit Type Of Package 1

PCE

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Number Of Units In Package 1

#### **Contractual warranty**

Warranty

18 months

1

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Eà

Transparency RoHS/REACh

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile