

Product data sheet

Specifications

SQUARE D



Circuit breaker, FA, 600V, 20A, 2 pole, 2 phase

FAB26020AC

Discontinued on: Jul 12, 2021

Discontinued

Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

Line Rated Current	20 A
Number Of Poles	2P
Breaking Capacity Code	A
Mounting Mode	Bolt-on
Magnetic Hold Current	275 A
Magnetic Tripping Current	600 A
Electrical Connection	I-Line connection, line Bolted connection, load
Terminal Identifier	AL50FA
Phase Connection	AC
Height	6.4 in (162.56 mm)
Width	3 in (76.20 mm)
Depth	4.13 in (104.90 mm)
Circuit Breaker Application	HACR rated

Environment

Certifications	UL Listed CSA
----------------	------------------

Ordering and shipping details

Category	01010-FA/FH 600V
Discount Schedule	DE2
Gtin	00785901530206
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
------------------------------	---

Contractual warranty

Warranty	18 months
----------	-----------