





Circuit breaker, FH, 277V 40A

FH16040B

- ! Discontinued on: Dec 8, 2020
- ! End-of-service on: Dec 31, 2020

(!) Discontinued

Main

Product Or Component Type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

•	
Line Rated Current	40 A
Number Of Poles	1P
Breaking Capacity Code	Н
Mounting Mode	I-Line
Magnetic Hold Current	400 A
Magnetic Tripping Current	850 A
Electrical Connection	Lugs, load I-Line connection, line
Terminal Identifier	AL100FA
Height	6.4 in (162.56 mm)
Width	1.5 in (38.10 mm)
Depth	4.13 in (104.90 mm)

Environment

0		
Certifications	CSA	
	UL Listed	

Ordering and shipping details

Category	01010-FA/FH 600V
Discount Schedule	DE2
Gtin	785901075981
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 10 in (5 334 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	7.70 in (19.558 cm)
Package 1 Length	12.90 in (32.766 cm)
Package 1 Weight	2.48 lb(US) (1.125 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Certifications & Standards

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

EU RoHS Declaration

Environmental Disclosure Product Environmental Profile