
Product data sheet

Specifications



Main

Product Or Component Type	Circuit breaker	
Trip Unit Technology	Thermal-magnetic	

Complementary

J	
Line Rated Current	60 A
Number Of Poles	1P
Breaking Capacity Code	н
Mounting Mode	I-Line
Magnetic Hold Current	800 A
Magnetic Tripping Current	1450 A
Electrical Connection	Lugs, load I-Line connection, line
Terminal Identifier	AL100FA
Height	6.4 in (162.56 mm)
Width	1.5 in (38.10 mm)
Depth	4.13 in (104.90 mm)

Environment

Certifications

UL Listed CSA

Ordering and shipping details

Category	01010-FA/FH 600V	
Discount Schedule	DE2	
Gtin	785901338055	
Returnability	No	
Country Of Origin	MX	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	6.42 in (16.3 cm)	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Package 1 Width	1.50 in (3.8 cm)	
Package 1 Length	4.13 in (10.5 cm)	
Package 1 Weight	2.47 lb(US) (1.12 kg)	

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

fa

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause Birth Defects or other reproductive harm.For more information go to www.p65warnings.ca.gov