Product data sheet

Specifications





Auxiliary contacts, TeSys GS, 1 NC, early break, front mounting, for GS2 with front/side handle

GS1AM101

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 22.05 USD

Main

Range Of Product	TeSys
Device Short Name	GS1AM
Product Or Component Type	Auxiliary contact
Contact Application	O, I and test position signalling
Range Compatibility	TeSys TeSys GS fuse-switch disconnector FuPact FuPacT GS fuse-switch disconnector
Contacts Type And Composition 1 NC	
Contact Operation	Early-break
[Ith] Conventional Free Air Thermal Current	10 A (at 104 °F (40 °C))
[le] Rated Operational Current	6 A 120 V AC-15 3 A 240 V AC-15 1.8 A 400 V AC-15 1.5 A 480 V AC-15 2.8 A 24 V DC-13 1.4 A 48 V DC-13 0.55 A 125 V DC-13 0.27 A 250 V DC-13 0.15 A 400 V DC-13

Complementary

Mechanical Durability	5 Mcycles	
Electrical Durability	1 Mcycles AC-15	
Switch Rated Current	30 A	
	32 A	
	50 A	
	60 A	
	63 A	
	100 A	
	125 A	
	160 A	
	200 A	
	250 A	
	315 A	
	400 A	
	600 A	
	630 A	
	800 A	
	1250 A	
Fuse Type	NFC	
	DIN	
	BS	
	CC	
	J	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Type Of Operating Handle	External frontal External right side External left side
Mounting Location	Front face
Net Weight	0.03 lb(US) (0.015 kg)

Ordering and shipping details

Category	US10I1122640	
Discount Schedule	0111	
Gtin	3389110181784	
Returnability	No	
Country Of Origin	FR	

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.59 in (1.5 cm)
Package 1 Width	2.36 in (6 cm)
Package 1 Length	3.15 in (8 cm)
Package 1 Weight	0.46 oz (13 g)
Unit Type Of Package 2	S01
Number Of Units In Package 2	10
Package 2 Height	5.91 in (15 cm)
Package 2 Width	5.91 in (15 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	11.01 oz (312 g)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Reach Free Of Svhc	
9	Toxic Heavy Metal Free	
②	Mercury Free	
⊘	Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov