Product data sheet

Specifications





TeSys Deca Manual Starter and Protector, auxiliary contact block, 1 NO and 1 NC, side mount, screw clamp

GVAN11

Product availability: Stock - Normally stocked in distribution facility

Price*: 35.70 USD

Main

Range	TeSys TeSys Deca
Device Short Name	GVAN
Product Or Component Type	Auxiliary contact block
Product Compatibility	GV2ME GV2RT GV2L GV3P GV3L GV2LE GV2P
Mounting Location	Left side
Pole Contact Composition	1 NO + 1 NC

Complementary

[Ui] Rated Insulation Voltage	600 V UL 508 690 V IEC 60947-1 600 V CSA C22.2 No 14
[Ue] Rated Operational Voltage	48690 V AC 24240 V DC
[Ith] Conventional Free Air Thermal Current	6 A
Mechanical Durability	100000 cycles
Minimum Switching Current	5 mA
Minimum Switching Voltage	17 V
Protection Type	GB2CB circuit breaker GG fuse 10 A
Rated Operational Power In Va	300 VA 48 V AC-15 100000 cycles 414 VA 690 V AC-15 100000 cycles 500 VA 110127 V AC-15 100000 cycles 500 VA 500 V AC-15 100000 cycles 650 VA 440 V AC-15 100000 cycles 720 VA 230240 V AC-15 100000 cycles 850 VA 380415 V AC-15 100000 cycles
Rated Operational Power In W	120 W 240 V DC-13 100000 cycles 140 W 110 V DC-13 100000 cycles 140 W 24 V DC-13 100000 cycles 180 W 60 V DC-13 100000 cycles 240 W 48 V DC-13 100000 cycles
Tightening Torque	12.39 lbf.in (1.4 N.m) screw clamp terminals

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Height	3.50 in (89 mm)	
Width	0.37 in (9.3 mm)	
Depth	2.60 in (66 mm)	
Net Weight	0.11 lb(US) (0.05 kg)	
Color	Dark grey	

Environment

Environmental Characteristic	Normal environment
Product Certifications	UKCA

Ordering and shipping details

Category	US10I1122367
Discount Schedule	0111
Gtin	3389110343489
Returnability	Yes
Country Of Origin	US

Packing Units

-	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.59 in (1.500 cm)
Package 1 Width	2.76 in (7.000 cm)
Package 1 Length	3.54 in (9.000 cm)
Package 1 Weight	1.62 oz (46.000 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	3.74 in (9.500 cm)
Package 2 Width	3.94 in (10.000 cm)
Package 2 Length	5.98 in (15.200 cm)
Package 2 Weight	17.99 oz (510.000 g)
Unit Type Of Package 3	S02
Number Of Units In Package 3	60
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	7.26 lb(US) (3.294 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc

Toxic Heavy Metal Free	
Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov

Product data sheet

Connections and Schema

GVAN11

