





Safety switch, heavy duty, fusible, 100A, 3 wire, 2 pole, 1 neutral, 30hp, 240VAC/250VDC, NEMA 1

H223N

! Discontinued on: Nov 22, 2023



Product availability: Non-Stock - Not normally stocked in distribution facility

Main

| Product | Single Throw Safety Switch |
|---------------------------|--|
| Duty Rating | Heavy duty |
| Device Application | Heavy application |
| Disconnect Type | Fusible disconnect |
| Factory Installed Neutral | Neutral (factory installed) |
| Phase | 3 phase |
| Number Of Poles | 2 |
| Current Rating | 100 A |
| Voltage Rating | 250 V DC 240 V AC |
| Enclosure Rating | NEMA 1 steel |
| Motor Power Hp | 7.5 hp at 240 V AC 50-60 Hz for 1 phase motors 15 hp at 240 V AC 50-60 Hz for 3 phase motors 15 hp at 240 V AC 50-60 Hz for 1 phase motors 30 hp at 240 V AC 50-60 Hz for 3 phase motors 20 hp at 250 V DC |

Complementary

| Short-Circuit Current | 10 kA for H or K |
|-----------------------|---|
| | 200 kA for R or J |
| Fuse Type | H or K |
| | R or J |
| Mounting Type | Surface |
| Electrical Connection | Lugs |
| Wiring Configuration | 3-wire |
| Wire Size | AWG 12AWG 1/0 aluminium |
| | AWG 14AWG 1/0 copper |
| Tightening Torque | 50 lbf.in (5.65 N.m) (AWG 1AWG 3/0) |
| | 45 lbf.in (5.08 N.m) (AWG 6AWG 4) |
| | 40 lbf.in (4.52 N.m) 0.01 in ² (8.367 mm ²) (AWG 8) |
| | 35 lbf.in (3.95 N.m) 0.000.01 in ² (2.065.261 mm ²) (AWG 14AWG 10) |
| Depth | 6.38 in (162.05 mm) |
| Width | 8.5 in (215.90 mm) |
| Height | 21.25 in (539.75 mm) |
| Net Weight | 19.84 lb(US) (9 kg) |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environment

Certifications UL listed file E2875

Ordering and shipping details

| Category | US10DE100008 | |
|-------------------|--------------|--|
| Discount Schedule | 0DE1 | |
| Gtin | 785901477877 | |
| Returnability | Yes | |
| Country Of Origin | US | |

Packing Units

| Unit Type Of Package 1 | PCE |
|------------------------------|-------------------------|
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 7.20 in (18.288 cm) |
| Package 1 Width | 10.70 in (27.178 cm) |
| Package 1 Length | 23.30 in (59.182 cm) |
| Package 1 Weight | 17.21 lb(US) (7.806 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |