






Safety switch, heavy duty, fusible, 30A, 3 wire, 3 pole, 20HP, 600V AC/DC, NEMA 12

H361AWK

! Discontinued on: Jun 23, 2023



Product availability: Stock - Normally stocked in distribution

Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Fusible disconnect
Factory Installed Neutral	None
Phase	3 phase
Number Of Poles	3
Current Rating	30 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 3R/12 galvannealed steel
Motor Power Hp	5 hp at 480 V AC 50-60 Hz for 3 phase motors 15 hp at 480 V AC 50-60 Hz for 3 phase motors 7.5 hp at 600 V AC 50-60 Hz for 3 phase motors 20 hp at 600 V AC 50-60 Hz for 3 phase motors 5 hp at 250 V DC 15 hp at 600 V DC

Complementary

Short-Circuit Current	10 kA for H or K	
	200 kA for R or J	
Fuse Type	H or K	
	R or J	
Mounting Type	Surface	
Electrical Connection	Lugs	
Wiring Configuration	3-wire (3P)	
Wire Size	AWG 12AWG 6 aluminium	
	AWG 14AWG 6 copper	
Tightening Torque	45 lbf.in (5.08 N.m) 0.02 in ² (13.3 mm ²) (AWG 6)	
	40 lbf.in (4.52 N.m) 0.01 in ² (8.367 mm ²) (AWG 8)	
	35 lbf.in (3.95 N.m) 0.000.01 in ² (2.065.261 mm ²) (AWG 14AWG 10)	
Depth	4.96 in (125.98 mm)	
Width	7.55 in (191.77 mm)	
Height	14.6 in (370.84 mm)	
Net Weight	11.02 lb(US) (5 kg)	

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environment

Certifications UL listed file E2875

Ordering and shipping details

Category	US10DE100113
Discount Schedule	0DE1
Gtin	785901481997
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.50 in (13.97 cm)
Package 1 Width	7.50 in (19.05 cm)
Package 1 Length	17.50 in (44.45 cm)
Package 1 Weight	10.58 lb(US) (4.8 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance




Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Compliant with Exemptions	
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.	
Environmental Disclosure	Product Environmental Profile	
Circularity Profile	No need of specific recycling operations	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov	

Dimensions Drawings

Approximate Dimensions



H361AWK

Connections and Schema

Connections and Wiring Diagrams

WIRING DIAGRAMS				
FUSIBLE		NOT FUSIBLE		
	1	7 9 9 <i>†-</i> †/		
H221AWK	H321AWK H361AWK	HU361AWK HU361AWKEI		