Product data sheet

Specifications



Safety switch, heavy duty, fusible, 30A, 600VAC, 600VDC, 3 poles, 20hp, NEMA 4, 4X, 5, 304 steel, Crouse-Hinds

H361DSWC

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 6,377.00 USD

Main

Product	Receptacle Switch
For Use With	Plug APJ3485 Crouse-Hinds Arktite
Disconnect Type	Fusible disconnect switch
Phase	3 phase
Number Of Poles	3
Current Rating	30 A
Voltage Rating	600 V AC 250 V DC
Enclosure Rating Nema 3R	NEMA 4/4X/5 stainless steel 304
Maximum Horse Power Rating	5 hp at 480 V AC 50-60 Hz for 3 phase motors 15 hp at 480 V AC 50-60 Hz for 3 phase motors 7.5 hp at 600 V AC 50-60 Hz for 3 phase motors 20 hp at 600 V AC 50-60 Hz for 3 phase motors 5 hp at 250 V DC

Complementary

Short-Circuit Current Rating	10 kA H or K
_	200 kA R or J
Fuse Type	H or K
	R or J
Mounting Type	Surface
Electrical Connection	Receptacle
Wire Configuration	4-wire
Wire Size	AWG 12AWG 2 aluminium
	AWG 14AWG 2 copper
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 6)
	40 lbf.in (4.52 N.m) (AWG 8)
	35 lbf.in (3.95 N.m) (AWG 14AWG 10)
Depth	5.11 in (129.79 mm)
Width	10.79 in (274.07 mm)
Height	16.87 in (428.50 mm)

Environment

Certifications

UL Listed

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10DE100118
Discount Schedule	0DE1
Gtin	785901369356
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	31.44 in (79.849 cm)
Package 1 Width	7.37 in (18.732 cm)
Package 1 Length	13.44 in (34.129 cm)
Package 1 Weight	23.00 lb(US) (10.433 kg)

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Mercury Free
Rohs Exemption Information Yes
Pvc Free

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov