






Safety switch, heavy duty, fusible, 30A, 4 wire, 3 pole, 1 neutral, 20hp, 600VAC/DC, NEMA 1

H361N

! Discontinued on: Jan 31, 2024



Product availability: Stock - Normally stocked in distribution

Main

| Product | Single Throw Safety Switch | |
|---------------------------|---|--|
| Duty Rating | Heavy duty | |
| Device Application | Heavy application | |
| Disconnect Type | Fusible disconnect | |
| Factory Installed Neutral | Neutral (factory installed) | |
| Phase | 3 phase | |
| Number Of Poles | 3 | |
| Current Rating | 30 A | |
| Voltage Rating | 600 V AC/DC | |
| Enclosure Rating | NEMA 1 steel | |
| Motor Power Hp | 5 hp at 480 V AC 50-60 Hz for 3 phase motors 15 hp at 480 V AC 50-60 Hz for 3 phase motors 7.5 hp at 600 V AC 50-60 Hz for 3 phase motors 20 hp at 600 V AC 50-60 Hz for 3 phase motors 15 hp at 600 V DC | |

Complementary

| Short-Circuit Current | 10 kA for H or K |
|-----------------------|---|
| | 200 kA for R or J |
| Fuse Type | H or K |
| | R or J |
| Mounting Type | Surface |
| Electrical Connection | Lugs |
| Wiring Configuration | 4-wire (3PH + N) |
| Wire Size | AWG 12AWG 6 aluminium |
| | AWG 14AWG 6 copper |
| Tightening Torque | 45 lbf.in (5.08 N.m) 0.02 in² (13.3 mm²) (AWG 6) |
| | 40 lbf.in (4.52 N.m) 0.01 in ² (8.367 mm ²) (AWG 8) |
| | 35 lbf.in (3.95 N.m) 0.000.01 in ² (2.065.261 mm ²) (AWG 14AWG 10) |
| Depth | 4.87 in (123.70 mm) |
| Width | 7.55 in (191.77 mm) |
| Height | 14.6 in (370.84 mm) |
| Net Weight | 8.82 lb(US) (4 kg) |

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environment

Certifications UL listed file E2875

Ordering and shipping details

| Category | US10DE100008 |
|-------------------|--------------|
| Discount Schedule | 0DE1 |
| Gtin | 785901481911 |
| Returnability | Yes |
| Country Of Origin | US |

Packing Units

| • | |
|------------------------------|-----------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 5.20 in (13.208 cm) |
| Package 1 Width | 7.80 in (19.812 cm) |
| Package 1 Length | 16.30 in (41.402 cm) |
| Package 1 Weight | 8.25 lb(US) (3.742 kg) |
| Unit Type Of Package 2 | PAL |
| Number Of Units In Package 2 | 120 |
| Package 2 Height | 45.50 in (115.57 cm) |
| Package 2 Width | 40.00 in (101.6 cm) |
| Package 2 Length | 48.00 in (121.92 cm) |
| Package 2 Weight | 1026.00 lb(US) (465.385 kg) |

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

| Reach Regulation | REACh Declaration |
|---------------------------|---|
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information. |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Dimensions Drawings

Approximate Dimensions

