





Safety switch, heavy duty, fusible, 60A, 600VAC, 600VDC, 3 poles, 50hp, NEMA 12K, Hubbellock receptacle

H362AWH

Product availability: Stock - Normally stocked in distribution facility

Price*: 2,459.00 USD

Main

Product	Receptacle Switch	
For Use With	Plug SD12781 Hubbellock	
Disconnect Type	Fusible disconnect switch	
Phase	3 phase	
Number Of Poles	3	
Current Rating	60 A	
Voltage Rating	600 V AC 250 V DC	
Enclosure Rating Nema 3R	NEMA 12K	
Maximum Horse Power Rating	15 hp at 480 V AC 50-60 Hz for 3 phase motors 30 hp at 480 V AC 50-60 Hz for 3 phase motors 15 hp at 600 V AC 50-60 Hz for 3 phase motors 50 hp at 600 V AC 50-60 Hz for 3 phase motors 10 hp at 250 V DC	

Complementary

Mounting Type	Surface	
Electrical Connection	Receptacle	
Wire Configuration	4-wire	
Wire Size	AWG 12AWG 2 aluminium AWG 14AWG 2 copper	
Tightening Torque	45 lbf.in (5.08 N.m) (AWG 6AWG 4) 40 lbf.in (4.52 N.m) (AWG 8) 35 lbf.in (3.95 N.m) (AWG 14AWG 10)	
Depth	7 in (177.80 mm)	
Width	10.5 in (266.70 mm)	
Height	16.5 in (419.10 mm)	
Net Weight	ht 17.64 lb(US) (8 kg)	

Environment

Certifications UL Listed

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Category	US10DE100119	
Discount Schedule	0DE1	
Gtin	785901482123	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	8.00 in (20.32 cm)	
Package 1 Width	14.00 in (35.56 cm)	
Package 1 Length	32.30 in (82.042 cm)	
Package 1 Weight	20.48 lb(US) (9.29 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

	Mercury Free	
	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov