





Safety switch, heavy duty, fusible, 60A, 3 wire, 3 pole, 50hp, 600VAC/DC, NEMA 12

H362AWK

! Discontinued on: Jan 31, 2024



Product availability: Stock - Normally stocked in distribution

Main

Product	Single Throw Safety Switch	
Duty Rating	Heavy duty	
Device Application	Heavy application	
Disconnect Type	Fusible disconnect	
Factory Installed Neutral	None	
Phase	3 phase	
Number Of Poles	3	
Current Rating	60 A	
Voltage Rating	600 V AC/DC	
Enclosure Rating	NEMA 3R/12 galvannealed steel	
Motor Power Hp	15 hp at 480 V AC 50-60 Hz for 3 phase motors 30 hp at 480 V AC 50-60 Hz for 3 phase motors 15 hp at 600 V AC 50-60 Hz for 3 phase motors 50 hp at 600 V AC 50-60 Hz for 3 phase motors 30 hp at 600 V DC	

Complementary

•		
Short-Circuit Current	10 kA for H or K	
	200 kA for R or J	
Fuse Type	H or K	
	R or J	
Mounting Type Surface		
Electrical Connection Lugs		
Wiring Configuration	Configuration 3-wire	
Wire Size	AWG 14AWG 3 copper	
	AWG 12AWG 3 aluminium	
Tightening Torque	50 lbf.in (5.65 N.m) (AWG 3)	
	45 lbf.in (5.08 N.m) (AWG 6AWG 4)	
	40 lbf.in (4.52 N.m) 0.01 in ² (8.367 mm ²) (AWG 8)	
	50 lbf.in (5.65 N.m) 0.000.01 in² (2.065.261 mm²) (AWG 14AWG 10)	
Depth	7 in (177.80 mm)	
Width	10.5 in (266.70 mm)	
Height	16.5 in (419.10 mm)	
et Weight 19.84 lb(US) (9 kg)		

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Environment

Certifications UL listed file E2875

Ordering and shipping details

Category	US10DE100113	
Discount Schedule	0DE1	
Gtin	785901482161	
Returnability	Yes	
Country Of Origin	US	

Packing Units

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	7.30 in (18.542 cm)	
Package 1 Width	10.80 in (27.432 cm)	
Package 1 Length	19.90 in (50.546 cm)	
Package 1 Weight	17.74 lb(US) (8.047 kg)	
Unit Type Of Package 2	pe Of Package 2 PAL	
Number Of Units In Package 2	40	
Package 2 Height	ge 2 Height 41.00 in (104.14 cm)	
Package 2 Width	2 Width 40.00 in (101.6 cm)	
Package 2 Length	48.00 in (121.92 cm)	
Package 2 Weight	732.00 lb(US) (332.029 kg)	

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

②	Mercury Free	
⊘	Rohs Exemption Information	Yes
⊘	Pvc Free	

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov