





Safety switch, heavy duty, fusible, 800A, 3 pole, 500hp, 600VAC/DC, NEMA 12

H367AWK

Product availability: Non-Stock - Not normally stocked in distribution facility

Price*: 16,352.00 USD

Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Fusible disconnect
Factory Installed Neutral	None
Phase	3 phase
Number Of Poles	3
Current Rating	800 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 3R/12 galvannealed steel
Motor Power Hp	200 hp at 480 V AC 50-60 Hz for 3 phase motors 500 hp at 480 V AC 50-60 Hz for 3 phase motors 250 hp at 600 V AC 50-60 Hz for 3 phase motors 500 hp at 600 V AC 50-60 Hz for 3 phase motors 50 hp at 600 V DC

Complementary

Short-Circuit Current	200 kA maximum for L
Fuse Type	L
Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	3-wire
Wire Size	AWG 3/0750 kcmil copper or aluminium
Tightening Torque	375 lbf.in (42.37 N.m) 0.130.59 in² (85.01380 mm²) (AWG 3/0750 kcmil)
Depth	17.75 in (450.85 mm)
Width	36.62 in (930.15 mm)
Height	69.13 in (1755.90 mm)
Net Weight	369.94 lb(US) (167.8 kg)

Environment

Certifications UL listed file E2875

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Ordering and shipping details

Category	US10DE100155
Discount Schedule	0DE1
Gtin	785901077022
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >


Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov