

# Product data sheet

Specifications



Surge protection device,  
Surgelogic, HL, 160kA, 208Y/120  
VAC, 3 phase, 4 wire, SPD type 2

HL2IMA16C

Product availability: Stock - Normally stocked in distribution facility

Price\*: 10,872.00 USD

## Main

Product	Surge protection device
Range	Surgelogic
Device Short Name	IMA
Type	HL

## Complementary

Voltage Rating	208Y/120 V AC
Mcov	150 V
Sccr	200 kA
Surge Current	160 kA
Rated Current	60 A
Breaking Capacity	50 kA
Number Of Phases	3 phase
Max Number Of Poles	3
Wiring Configuration	4-wire
Connection	I-Line line Lugs ground AWG 6 copper 35.40 lbf.in (4 N.m) Lugs neutral AWG 6 copper 35.40 lbf.in (4 N.m)
Trip Unit Technology	Thermal-magnetic
Local Signalling	Status LED green per phase normal operation Status LED red per phase fault
Provided Equipment	Alarm enable/disable switch Surge counter Circuit-breaker
Cable Length	19.02 in (483 mm)
Mounting Support	Panel mounting
Height	12.16 in (308.9 mm)
Width	13.46 in (341.9 mm)
Depth	5.59 in (142.1 mm)

## Environment

Enclosure Rating	NEMA 2
------------------	--------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	UL 1449:ed. 3 UL 1283:ed. 5 CSA C22.2 No 8:1986 UL 96A:ed. 12 UL 489:ed. 11 CSA C22.2 No 5-09
-----------	--

## Ordering and shipping details

Category	US1DE1B08460
Discount Schedule	DE1B
Gtin	785901679127
Returnability	Yes
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	9.00 in (22.86 cm)
Package 1 Width	16.00 in (40.64 cm)
Package 1 Length	17.50 in (44.45 cm)
Package 1 Weight	22.19 lb(US) (10.064 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

 Rohs Exemption Information	Yes
Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>