Product data sheet

Specification





base unit, Harmony GTU, open box, 32GB CFast card

HMIG5U2

Product availability: Stock - Normally stocked in distribution facility

Price*: 1,764.27 USD

Main

Range Of Product	Harmony GTU
Product Or Component Type	Base unit
Device Short Name	Open Box
Range Compatibility	Harmony GTU
[Us] Rated Supply Voltage	1224 V DC power supply

Complementary

Integrated Connection Type	Ethernet TCP/IP 2 RJ45 COM1 serial link RJ45 RS485 110115200 bit/s COM2 serial link SUB-D 9 RS232C/RS422/RS485 110115200 bit/s Auxiliary port terminal block Expansion unit fieldbus card USB 2.0 port mini B USB DVI-D video port DVI-D Microphone mini-jack USB 2.0 port 3 USB type A
Communication Port Protocol	Modbus Modbus TCP/IP Uni-Telway
Operating System	Windows Embedded 7
Software Package	Internet Explorer Vijeo Citect web client Vijeo Designer run time .NET framework 4.0 Adobe PDF reader Multimedia player Office reader VNC client/server
Processor Name	Intel X86 1.33 GHz
Data Storage Equipment	32 GB CFast card
Port Ethernet	10BASE-T/100BASE-TX/1000BASE-T
Memory Description	512 KB NVRAM backup memory 2 GB RAM internal
Type Of Cooling	Natural convection
Width	7.40 in (188 mm)
Height	5.16 in (131 mm)
Depth	1.77 in (45 mm)
Net Weight	1.98 lb(US) (0.9 kg)

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Standards	CSA C22.2 No 142 ANSI/ISA 12-12-01 UL 508 Class I division 2 CSA C22.2 No 213
	IEC 61132-2
Product Certifications	CE CULus ATEX IEC-Ex RCM GL KC CUL EAC ABS BV CCS DNV LR RINA UKCA UKEX
Ambient Air Temperature For Operation	32140 °F (060 °C)
Ambient Air Temperature For Storage	-4140 °F (-2060 °C)
Pollution Degree	2 IEC 61131-2 ed.3
Relative Humidity	1090 % non-condensing
Operating Altitude	2000
Vibration Resistance	3.5 mm constant amplitude 59 Hz) IEC 61131-2 9.8 m/s² 9150 Hz) IEC 61131-2
Electromagnetic Compatibility	Electrostatic discharge immunity test level 3 conforming to IEC 61000-4-2

Ordering and shipping details

Category	US10MC222567
Discount Schedule	0MC2
Gtin	3606481213785
Returnability	Yes
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.16 in (13.1 cm)
Package 1 Width	8.27 in (21.0 cm)
Package 1 Length	10.24 in (26.0 cm)
Package 1 Weight	2.78 lb(US) (1.262 kg)
Unit Type Of Package 2	S04
Number Of Units In Package 2	4
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	15.75 in (40.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Package 2 Weight	12.92 lb(US) (5.862 kg)

Number Of Units In Package 3	48
Package 3 Height	31.50 in (80.0 cm)
Package 3 Width	47.24 in (120.0 cm)
Package 3 Length	41.34 in (105.0 cm)
Package 3 Weight	174.92 lb(US) (79.344 kg)

Contractual warranty

Warranty 18 months

Sustainability Green Premium

Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Weee Circularity Profile	· · · · · · · · · · · · · · · · · · ·


HMIG5U2

Dimensions Drawings

Dimensions

External Dimensions





- 1 Front
- 2 Left
- 3 Bottom