





Mini circuit breaker, Homeline, 15A, 1 pole, 120/240VAC, 10kA AIR, standard type, plug in, UL

HOM115C

Product availability: Stock - Normally stocked in distribution

Price*: 27.62 USD

Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	15 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Short Circuit Current Rating	10 kA
Number Of Spaces	1
Circuit Breaker Type	Standard
Ratings	HACR and Switching Duty rated
Electrical Connection	Screw clamp terminals
Wire Size	1 x AWG 14AWG 8 (aluminium/copper) 2 x AWG 14AWG 10 (copper)
Type Of Packing	Clam packaging

Complementary

Tightening Torque	35.40 lbf.in (4.0 N.m) 0.000.01 in² (2.56 mm²) (AWG 14AWG 8)
Height	3.13 in (79.50 mm)
Width	1 in (25.40 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient Air Temperature For $$104\ ^{\circ}\text{F}$ (40\ ^{\circ}\text{C})$$ Operation

Ordering and shipping details

Category	US10CPH01320	
Discount Schedule	ОСРН	
Gtin	047569062872	
Returnability	Yes	
Country Of Origin	US	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Packing Units

9	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.20 in (3.048 cm)
Package 1 Width	4.50 in (11.43 cm)
Package 1 Length	4.30 in (10.922 cm)
Package 1 Weight	5.12 oz (145.15 g)
Unit Type Of Package 2	PAL
Number Of Units In Package 2	2304
Package 2 Height	40.00 in (101.6 cm)
Package 2 Width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)
Package 2 Weight	826.74 lb(US) (375.004 kg)

Contractual warranty

Warranty Lifetime



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations