





Load center, Homeline, 1 phase, 12 spaces, 24 circuits, 125A convertible main lugs, PoN, NEMA1, gnd bar, value pack

HOM1224L125PGCVP

Product availability: Stock - Normally stocked in distribution facility

Price\*: 309.00 USD

### Main

Product Type	Load Center	
Marketing Trade Name	Homeline	
Load Center Type	PoN Convertible Mains (lugs)	
Rated Current	125 A	
Number Of Spaces	12	
Maximum Number Of Single Pole Circuits	24	
Enclosure Rating	NEMA 1 indoor	
Cover Type	Combination flush/surface cover	
Electrical Connection	Lugs	
Provided Equipment	Grounding bar 1) Circuit-breaker 2) 1P 20 A 120/240 V AC	

## Complementary

Max Short Circuit Current Rating	10 kA	
Maximum Number Of Tandem Breakers	6	
Number Of Phases	1 phase	
Voltage Rating	120/240 V AC	
Wire Size	AWG 6AWG 2/0 aluminium AWG 6AWG 1 copper	
Ground Bar	Grounding bar included (not installed)	
Wiring Configuration	3-wire	
Busbar Material	Tin plated aluminium: busbar	
Enclosure Material	Welded galvannealed steel	
Surface Finish	Baked enamel Gray	
Box Number	6	
Bus Rated Current	125.0 A	
Height	17.91 in (455 mm)	
Width	14.25 in (362 mm)	
Depth	3.74 in (95 mm)	

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## **Environment**

Ambient Air Temperature For Operation	23 °F (-5 °C) 104 °F (40 °C)
Product Certifications	UL listed file E-6294

# Ordering and shipping details

Category	US1DE3C00185
Discount Schedule	DE3C
Gtin	785901864288
Returnability	Yes
Country Of Origin	US

# **Packing Units**

Unit Type Of Package 1	PCE	
Number Of Units In Package 1	1	
Package 1 Height	5.70 in (14.478 cm)	
Package 1 Width	16.10 in (40.894 cm)	
Package 1 Length	20.60 in (52.324 cm)	
Package 1 Weight	18.15 lb(US) (8.233 kg)	
Unit Type Of Package 2	PAL	
Number Of Units In Package 2	42	
Package 2 Height	40.00 in (101.6 cm)	
Package 2 Width	40.00 in (101.6 cm)	
Package 2 Length	45.00 in (114.3 cm)	
Package 2 Weight	773.00 lb(US) (350.627 kg)	

# **Contractual warranty**

Warranty 18 months



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

### Well-being performance

<b>②</b>	Toxic Heavy Metal Free	
<b>⊘</b>	Mercury Free	
<b>⊘</b>	Rohs Exemption Information	Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration  Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov