

# Product data sheet

Specifications

SQUARE D

Green Premium™



Mini circuit breaker, Homeline, 40A, 1 pole, 120/240VAC, 10kA AIR, standard type, plug in, UL

HOM140CP

Product availability: Stock - Normally stocked in distribution facility

Price\*: 26.30 USD

## Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	40 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	1P
Short Circuit Current Rating	10 kA
Number Of Spaces	1
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	1 x AWG 8...AWG 2 ( aluminium/copper )
Type Of Packing	Consumer packaging

## Complementary

Tightening Torque	40.71 lbf.in (4.6 N.m) (AWG 8...AWG 2)
Height	3.13 in (79.50 mm)
Width	1 in (25.40 mm)
Depth	2.98 in (75.69 mm)

## Environment

Ambient Air Temperature For Operation	104 °F (40 °C)
---------------------------------------	----------------

## Ordering and shipping details

Category	US10CPH01321
Discount Schedule	0CPH
Gtin	047569062735
Returnability	Yes
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.00 in (2.54 cm)
Package 1 Width	3.00 in (7.62 cm)
Package 1 Length	3.30 in (8.382 cm)
Package 1 Weight	5.44 oz (154.221 g)

## Contractual warranty

Warranty	Lifetime
----------	----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

Toxic Heavy Metal Free

Mercury Free

Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations