





Mini circuit breaker, Homeline, 30A, 2 pole, 120/240VAC, 10kA AIR, standard type, plug in, UL

HOM230C

Product availability: Stock - Normally stocked in distribution

Price*: 63.51 USD

Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	30 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	2P
Short Circuit Current Rating	10 kA
Number Of Spaces	2
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Clamp terminal for 2 cables
Wire Size	1 x AWG 14AWG 8 (aluminium/copper) 2 x AWG 14AWG 10 (copper)
Type Of Packing	Clam packaging

Complementary

Tightening Torque	35.40 lbf.in (4.0 N.m) 0.000.02 in² (2.510 mm²) (AWG 16AWG 14) 35.40 lbf.in (4.0 N.m) 0.010.03 in² (420 mm²) (AWG 12AWG 4)
Height	3.13 in (79.50 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient Air Temperature For $$104\ ^{\circ}\text{F}\ (40\ ^{\circ}\text{C})$}$ Operation

Ordering and shipping details

Category	US10CPH01345
Discount Schedule	ОСРН
Gtin	047569071003
Returnability	Yes

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Country Of Origin US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.10 in (5.334 cm)
Package 1 Width	3.90 in (9.906 cm)
Package 1 Length	4.30 in (10.922 cm)
Package 1 Weight	11.52 oz (326.587 g)



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

✓ Toxic Heavy Metal Free
 ✓ Mercury Free
 ✓ Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations