

Product data sheet

Specifications



Mini circuit breaker, Homeline,
40A, 2 pole, 120/240VAC, 10kA
AIR, standard type, plug in, UL

HOM240

Product availability: Stock - Normally stocked in distribution facility

Price*: 60.00 USD

Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	40 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number Of Poles	2P
Short Circuit Current Rating	10 kA
Number Of Spaces	2
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	1 x AWG 8...AWG 2 (aluminium/copper)

Complementary

Tightening Torque	40.71 lbf.in (4.6 N.m) (AWG 8...AWG 2)
Height	3.13 in (79.50 mm)
Width	2 in (50.80 mm)
Depth	2.98 in (75.69 mm)

Environment

Ambient Air Temperature For Operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	US1DE3D00046
Discount Schedule	DE3D
Gtin	785901065302
Returnability	Yes
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.60 in (4.06 cm)
Package 1 Width	2.60 in (6.6 cm)
Package 1 Length	3.10 in (7.87 cm)
Package 1 Weight	11.20 oz (317.52 g)
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	3.20 in (8.128 cm)
Package 2 Width	2.60 in (6.604 cm)
Package 2 Length	10.20 in (25.908 cm)
Package 2 Weight	3.58 lb(US) (1.624 kg)
Unit Type Of Package 3	CAR
Number Of Units In Package 3	50
Package 3 Height	10.40 in (26.416 cm)
Package 3 Width	6.90 in (17.526 cm)
Package 3 Length	16.60 in (42.164 cm)
Package 3 Weight	36.65 lb(US) (16.624 kg)

Contractual warranty

Warranty	Lifetime
----------	----------

Sustainability



Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.




[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

 Toxic Heavy Metal Free	
 Mercury Free	
 Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations